



D

PORT 1 PORT 2



1. INSERTION LOSS: ST <= 0.5dB
LC <= 0.3dB
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS
OF TYCO ELECTRONICS STANDARD 230-702.

C



B

14.85-15.15 [584.65-596.46]	1-1754796-5
9.85-10.15 [387.80-399.61]	1-1754796-0
4.85-5.15 [190.94-202.76]	1754796-5
2.85-3.15 [112.20-124.02]	1754796-3
1.85-2.15 [72.83-84.65]	1754796-2
0.85-1.15 [33.46-45.28]	1754796-1
L METERS [INCHES]	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.W.DAVIS	28OCT04	<div><div>tyco</div><div>Electronics</div></div> <div>Tyco Electronics Corporation Harrisburg, Pa 17105-3608</div>				
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN	28OCT04					
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD F.McCORKEL	28OCT04	NAME CABLE ASSEMBLY, FIBER OPTIC, 62.5/125um, OFNR, 1.8mm CABLE LC DUPLEX TO DUAL ST				
<div><div><div></div></div><div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± -</div><div>3 PLC ± -</div><div>4 PLC ± -</div><div>ANGLES ± -</div><div>FINISH</div></div></div>		PRODUCT SPEC —	APPLICATION SPEC —					
MATERIAL —	—	WEIGHT —	—	SIZE A2	CAGE CODE 00779	DRAWING NO C-1754796	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS	SHEET 1 OF 1	REV C

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-790142-2](#)