

4



3

2

1

LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	OWN
			C	REVISED PER ECR-05-015300	10NOV05	FM

1. INSERTION LOSS <= 0.3dB.
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.



14.85-15.15 [584.65-596.46]	1-1754810-5
9.85-10.15 [387.80-399.61]	1-1754810-0
4.85-5.15 [190.94-202.76]	1754810-5
2.85-3.15 [112.20-124.02]	1754810-3
1.85-2.15 [72.83-84.65]	1754810-2
0.85-1.15 [33.46-45.28]	1754810-1
L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.W.DAVIS 28OCT04	<b>tyco</b> Tyco Electronics Corporation <b>Electronics</b> Harrisburg, Pa 17105-3608	
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 28OCT04		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F.McCORKEL 28OCT04	NAME CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE, OFNR, 3.0mm CABLE DUAL ST TO DUAL ST	
	0 PLC ± -	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
	1 PLC ± -	APPLICATION SPEC		
	2 PLC ± -	—	A2 00779 C-1754810	
	3 PLC ± -	—		
	4 PLC ± -	—	CUSTOMER DRAWING	
	ANGLES ± -	—		
MATERIAL	FINISH	WEIGHT	SCALE NTS SHEET 1 OF 1 REV C	
—	—	—		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[6-2064389-5](#)