


Restricted to: General Release


USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT



Left Side

Connector(s): MT-RJ (No Pins)
Mode: MM
Housing Color: Black
Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - - - - - B
Fiber B - - - - - A

Notes:

- 1 Includes dust caps (not shown on print).
- 2 IL tested at 1300nm.
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Product and Processing must meet requirements of Tyco Electronics Standard 230-702


Right Side

Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Yellow
Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

	A	Rev Per EC#	RELEASE	0/23/2006	-		DF		
P	LTR	REVISION RECORD		DATE	DIN	APVD			



Customer Print

DWG Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Dave Fennell	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
AP'D	Dave Fennell			
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 1907126	1 of 4	A

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

USED ON

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	0/23/2006	-	DF
P	LTR	REVISION RECORD		DATE	DIN	APVD

DIMENSIONS; meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:	
	0 PLC	± -
	1 PLC	± -
	2 PLC	± -
	3 PLC	± -
	4 PLC	± -

DW Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Dave Fennell	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Dave Fennell			
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE NTS	SIZE A2	DRAWING NO C- 1907126	SHEET 2 of 4	REV A

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16


CAC Customer Layout Rev: D

THIS DRAWING IS A CONTROLLED DOCUMENT.

Restricted to: General Release

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex Secure, Yellow	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1907126-3	42.570 - 43.430	139.66 - 142.48	0.56	20	0.56	-
4-1907126-4	43.560 - 44.440	142.91 - 145.80	0.57	20	0.57	-
4-1907126-5	44.550 - 45.450	146.16 - 149.11	0.57	20	0.57	-
4-1907126-6	45.540 - 46.460	149.40 - 152.42	0.57	20	0.57	-
4-1907126-7	46.530 - 47.470	152.65 - 155.74	0.57	20	0.57	-
4-1907126-8	47.520 - 48.480	155.90 - 159.05	0.57	20	0.57	-
4-1907126-9	48.510 - 49.490	159.15 - 162.36	0.57	20	0.57	-
5-1907126-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-
5-1907126-1	50.490 - 51.510	165.64 - 168.99	0.58	20	0.58	-
5-1907126-2	51.480 - 52.520	168.89 - 172.30	0.58	20	0.58	-
5-1907126-3	52.470 - 53.530	172.14 - 175.62	0.58	20	0.58	-
5-1907126-4	53.460 - 54.540	175.39 - 178.93	0.58	20	0.58	-
5-1907126-5	54.450 - 55.550	178.64 - 182.25	0.58	20	0.58	-
5-1907126-6	55.440 - 56.560	181.88 - 185.56	0.58	20	0.58	-
5-1907126-7	56.430 - 57.570	185.13 - 188.87	0.59	20	0.59	-
5-1907126-8	57.420 - 58.580	188.38 - 192.19	0.59	20	0.59	-
5-1907126-9	58.410 - 59.590	191.63 - 195.50	0.59	20	0.59	-
6-1907126-0	59.400 - 60.600	194.88 - 198.81	0.59	20	0.59	-
6-1907126-1	60.390 - 61.610	198.12 - 202.13	0.59	20	0.59	-
6-1907126-2	61.380 - 62.620	201.37 - 205.44	0.59	20	0.59	-
6-1907126-3	62.370 - 63.630	204.62 - 208.75	0.59	20	0.59	-
6-1907126-4	63.360 - 64.640	207.87 - 212.07	0.6	20	0.6	-
6-1907126-5	64.350 - 65.650	211.12 - 215.38	0.6	20	0.6	-
6-1907126-6	65.340 - 66.660	214.37 - 218.70	0.6	20	0.6	-
6-1907126-7	66.330 - 67.670	217.61 - 222.01	0.6	20	0.6	-
6-1907126-8	67.320 - 68.680	220.86 - 225.32	0.6	20	0.6	-
6-1907126-9	68.310 - 69.690	224.11 - 228.64	0.6	20	0.6	-
7-1907126-0	69.300 - 70.700	227.36 - 231.95	0.61	20	0.61	-
7-1907126-1	70.290 - 71.710	230.61 - 235.26	0.61	20	0.61	-
7-1907126-2	71.280 - 72.720	233.85 - 238.58	0.61	20	0.61	-
7-1907126-3	72.270 - 73.730	237.10 - 241.89	0.61	20	0.61	-
7-1907126-4	73.260 - 74.740	240.35 - 245.20	0.61	20	0.61	-
7-1907126-5	74.250 - 75.750	243.60 - 248.52	0.61	20	0.61	-
7-1907126-6	75.240 - 76.760	246.85 - 251.83	0.61	20	0.61	-
7-1907126-7	76.230 - 77.770	250.09 - 255.15	0.62	20	0.62	-
7-1907126-8	77.220 - 78.780	253.34 - 258.46	0.62	20	0.62	-
7-1907126-9	78.210 - 79.790	256.59 - 261.77	0.62	20	0.62	-
8-1907126-0	79.200 - 80.800	259.84 - 265.09	0.62	20	0.62	-

	A	Rev Per EC#	RELEASE	0/23/2006	-	DF	
P	LTR	REVISION RECORD		DATE	DIN	APVD	



DIMENSIONS:
meters

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .


Customer Print

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Dave Fennell	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Dave Fennell			
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE NTS	SIZE A2	DRAWING NO C- 1907126	SHEET 3 of 4	REV A

8 7 6 5 4 3 2 1


USED ON

Per specification 107-1645-1



This label is used on all lengths on this drawing.

Per specification 107-1645-1



This label is used on all lengths on this drawing.

LOC
CE
DIST
16

	A	Rev Per EC#	RELEASE	D/23/2006	- DF
P	LTR	REVISION RECORD		DATE	DIN APVD

DIMENSIONS;
meters



Customer Print

TOLERANCES UNLESS OTHERWISE SPECIFIED:		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

QTN Cable Assy Configurator		MATERIAL -	HEAT TREAT
CHK Dave Fennell	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD Dave Fennell			
NAME FO C/A - 2 fiber, 62/125, OFNR (Riser) jacket, MT-RJ (No Pins)			
DESCRIPTION To LC-Duplex Secure			
SCALE NTS	SIZE A2	DRAWING NO C- 1907126	SHEET 4 of 4
			REV A

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure
------	--

SCALE NTS	SIZE A2	DRAWING NO C- 1907126	SHEET 4 of 4	REV A
--------------	------------	--------------------------	-----------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1906690-3](#)