




- 1

MAXIMUM CONNECTOR LOSS IS EQUAL TO 0.50dB PLUS CABLE ATTENUATION.
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.
- 3

SECOND TRACE LABEL WILL NOT BE PRESENT ON ANY CABLE ASSEMBLY THAT IS LESS THAN 1 METER IN LENGTH.
4. A COPY OF TEST DATA WILL BE PLACED INSIDE OR WITH THE UNIT PACKAGE.



FIBER COLOR	MT-RJ JACK POSITION	MT-RJ PLUG POSITION
BLUE	A	B
ORANGE OR NATURAL	B	A



VIEW D-D
NOT TO SCALE

1.05	30.00±0.30	[1181.11±11.81]	3-1985480-0
1.04	25.00±0.30	[984.25±11.81]	2-1985480-5
1.03	20.00±0.30	[787.40±11.81]	2-1985480-0
1.03	17.00±0.30	[669.29±11.81]	1-1985480-7
1.02	15.00±0.15	[590.55±5.91]	1-1985480-5
1.02	14.00±0.15	[551.18±5.91]	1-1985480-4
1.02	12.00±0.15	[472.44±5.91]	1-1985480-2
1.02	10.00±0.15	[393.70±5.91]	1-1985480-0
1.01	9.00±0.15	[354.33±5.91]	1985480-9
1.01	6.00±0.08	[236.22±3.15]	1985480-6
1.01	5.00±0.08	[196.85±3.15]	1985480-5
1.00	3.00±0.05	[118.11±1.97]	1985480-3
1.00	2.00±0.05	[78.74±1.97]	1985480-2
1.00	1.00±0.05	[39.37±1.97]	1985480-1
CABLE ASSEMBLY LOSS (dB)		L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

APPROVED

WEIGHT
-

CUSTOMER DRAWING

25SEP07
D. FENNELL

25SEP07
D. FENNELL

25SEP07
D. FENNELL

NAME
CABLE ASSEMBLY, FIBER OPTIC, OFNP, 62.5/125um, MT-RJ PLUG, NON-SECURE TO MT-RJ JACK WITH PINS, BLUE SECURE OPTIONS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1985480

RESTRICTED TO
-

SCALE
1:1

SHEET
1 of 1

REV
A

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-6278884-0](#)