

**DFMM-STST-XX**

xxM ST/ST MM 62.5/125, DUPLEX RISER

QTY. 1

www.bb-elec.com**DETAIL A****NOTES:**

1. INSERTION LOSS < 0.5dB.
2. OPERATION TEMP: -20°C TO +60°C
3. ORANGE PVC OUTER JACKET
4. INDIVIDUALLY BAGGED AND LABELED, (SEE DETAIL A)

CHART

DFMM-STST-10M	10	32.8'(10000)	+2"/-0(+50/-0)	
DFMM-STST-5M	5	16.4'(5000)	+2"/-0(+50/-0)	
DFMM-STST-3M	3	9.84'(3000)	+2"/-0(+50/-0)	
DFMM-STST-2M	2	6.56'(2000)	+2"/-0(+50/-0)	
DFMM-STST-1M	1	3.28'(1000)	+2"/-0(+50/-0)	
PART NO.	XX	L	T	BARCODE

B&B Electronics manufacturing Co.

	UNIT: Inches[mm]	TITLE: xxM DUPLEX 62.5/125 MULTIMODE ST/ST RISER JUMPER CABLE		
	DATE 05/09/2008			
DRAWN BY A. MEDINA	DATE	DRAWING NO. C.D. 2379		REV. A
CHECKED BY	DATE	REF:		
APPROVED BY	DATE	PART NO. DFMM-STST-XX		
P.O. NO.:	DATE			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&B Electronics:](#)

[DFMM-STST-1M](#) [DFMM-STST-2M](#)