



CQB50W12 SERIES

30-50 WATT 12:1 INPUT

DC-DC CONVERTERS

FEATURES

- * 30-50W Isolated Output
- * Efficiency to 89%
- * Fixed Switching Frequency
- * 12:1 Input Range
- * Regulated Outputs
- * Remote On/Off
- * Low No Load Power Consumption
- * Over Temperature Protection
- * Over Voltage/Current Protection
- * Continuous Short Circuit Protection
- * Quarter Brick Size Meet Industrial Standard
- * CE Mark Meets 2014/30/EU
- * UL60950-1 2nd (Basic Insulation) Approval
- * Meet EN50155 with External Circuits
- * Shock & Vibration Meets EN50155 (EN61373)
- * Fire & Smoke Meet EN45545-2
- * 5000m Operating Altitude



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.		CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD	(1)	(2)	
CQB50W12-72S05	14-160 VDC	5 VDC	0 mA	6.0 A	5 mA	530 mA	83	81	10000uF
CQB50W12-72S12	14-160 VDC	12 VDC	0 mA	4.2 A	5 mA	810 mA	87	86	6800μF
CQB50W12-72S24	14-160 VDC	24 VDC	0 mA	2.1 A	5 mA	810 mA	89	87	3300μF
CQB50W12-72S48	14-160 VDC	48 VDC	0 mA	1.05 A	8 mA	810 mA	88	85	680μF

NOTE:

1. Nominal Input Voltage 72 VDC
2. Measured at 110Vin

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[CQB50W12-72S05](#) [CQB50W12-72S12](#) [CQB50W12-72S24](#) [CQB50W12-72S48](#)