



0603 Ultra thin SMD LED

0.3 mm to 0.35 mm Height



PART NO.	DESCRIPTION	Distributor Cost, US\$
LTST-C194KGKT	SMD, AlInGaP Green, 0603, 0.3 mmH, 574 NM, 45 MCD, CLR, T&R	0.037
LTST-C194KFKT	SMD, AlInGaP Amber, 0603, 0.3 mmH, 605 NM, 180 MCD, CLR, T&R	0.037
LTST-C194KRKT	SMD, AlInGaP Red, 0603, 0.3 mmH, 631 NM, 112 MCD, CLR, T&R	0.037
LTST-C194KSKT	SMD, AlInGaP Yellow, 0603, 0.3 mmH, 589 NM, 112 MCD, CLR, T&R	0.037
LTST-C194TBKT	SMD, InGaN Blue, 0603, 0.3 mmH, 470 NM, 112 MCD, CLR, T&R	0.100
LTST-C194TGKT	SMD, InGaN Green, 0603, 0.3 mmH, 525 NM, 355 MCD, CLR, T&R	0.200
LTW-C194TS5	SMD, InGaN White, 0603, 0.3 mmH, 80 MCD @ 5 mA, T&R	0.085
LTST-C193KGKT-5A	SMD, AlInGaP Green, 0603, 0.35 mmH, 571 NM, 18 MCD @ 5 mA, CLR, T&R	0.037
LTST-C193KFKT-5A	SMD, AlInGaP Amber, 0603, 0.35 mmH, 605 NM, 45 MCD @ 5 mA, CLR, T&R	0.037
LTST-C193KRKT-5A	SMD, AlInGaP Red, 0603, 0.35 mmH, 631 NM, 28 MCD @ 5 mA, CLR, T&R	0.037
LTST-C193KSKT-5A	SMD, AlInGaP Yellow, 0603, 0.35 mmH, 589 NM, 28 MCD @ 5 mA, CLR, T&R	0.037
LTST-C193TBKT-5A	SMD, InGaN Blue, 0603, 0.35 mmH, 470 NM, 35 MCD @ 5 mA, CLR, T&R	0.100
LTST-C193TGKT-5A	SMD, InGaN Green, 0603, 0.35 mmH, 525 NM, 180 MCD @ 5 mA, CLR, T&R	0.200
LTW-C193TS5	SMD, InGaN White, 0603, 0.35 mmH, 80 MCD @ 5 mA, T&R	0.108

Detail specification is available upon request

Features Highlight -

- Ultra thin, z-height 0.3 mm and 0.35 mm
- 0603 footprint, IR reflow compatible
- Standard EIA tape and reel packaging
- High light output, Energy saving
- Pb-free and RoHS compliance

Applications -

- Hand-held devices, PDA
- Cell phones, Digital cameras
- Keypad backlight, Icon backlight
- Computer network systems
- Status indicators

