

Amphenol®



RIG-Lok

Amphenol, which has been manufacturing connectors for more than 75 years, offers an extensive array of connector lines including rectangular, circular, fiber optic, EMI/EMP filter and a variety of special application connectors.

With the introduction of its patented RADSOK technology, Amphenol Industrial Operations (AIO) revolutionized the connector industry. RADSOK'S twisted grid configuration allows for 50% more current to pass through the same size pin, while providing increased reliability, ampacity and cycle durability as well as lower insertion force, T-rise and voltage drop.

Features

- Ruggedized over-molded coupling nut
- Wire gages 4/0 awg through 777 MCM
- Utilizes patented Radsok Technology
- 1/4 Turn Reverse Bayonet
- Crimp or Busbar Termination
- Silver Plated Contacts
- Finger Proof
- Current: 800Amp
- Voltage: DC 2500V
- Operating Temperature: -40°C to +125°C
- 2000 Mating Cycles
- 300 Day Salt Spray Rating

The RIG-Lok is a reverse bayonet connector which incorporates our patented RADSOK technology. It is designed to deliver high power from source to load. The plug contains an 18mm RADSOK socket and the receptacle contains an 18mm pin with the option of crimp, 2 hole busbar, or threaded busbar termination. When unmated, personal safety is maintained through touchproof, dead-front contact design. The RADSOK'S strongest benefit is its very low milli-volt drop and minimized temperature rise when transmitting high current. The 18mm RIG-Lok is perfectly suited for high amperage applications such as electrical generators, fuel cells, load banks, and charging systems.



Benefits:

- Quick positive coupling
- Vibration resistant
- Audible, tactile and visual indication of full coupling
- Environmental Applications
- High Amperage Applications
- Easily Adaptable
- Better Conductivity where needed
- Allows conductor size change
- Hardware options include plugs, inline receptacle, and panel mount receptacles

Example Plug Part Number: V-06G-E-M50-7-N-BL

Example Receptacle Part Number: V-03B-E-N-BL

V = Vortex GT Connector

1 =	06G	Plug with Crimp Socket Contact
	03C	Receptacle with Crimp Pin Contact
	03B	Receptacle with 2 Hole Busbar Pin Contact
	01C	Inline Receptacle with Crimp Pin Contact
2 =	Omit	No Protective Cap
	E	Protective Cap
3 =	Omit	Plug or Receptacle Without Rear Hardware
	M40	Metric M40 Cable Adapter With Gland .748-1.102"
	M50	Metric M50 Cable Adapter With Gland 1.063-1.378"
	M63	Metric M50 Cable Adapter With Gland 1.339-1.772"
4 =	Omit	Threaded or 2 Hole Busbar Receptacles
		1 120 mm sq and 4/0awg crimp wire well
		2 150 mm sq and 262MCM crimp wire well
		3 185 mm sq and 313MCM crimp wire well
		4 200 mm sq and 373MCM crimp wire well
		5 240 mm sq and 444MCM crimp wire well
		6 535 MCM crimp wire well
		7 646 MCM crimp wire well
		8 777 MCM crimp wire well
5 =	N	180° Normal Rotation, Keyed Receptacle Shell and Slotted Plug
	J	360° Rotation, No Keyways
	W	120° Alternate Rotation, Keyed Receptacle Shell and Slotted Plug
	X	90° Alternate Rotation, Keyed Receptacle Shell and Slotted Plug
	Y	210° Alternate Rotation, Keyed Receptacle Shell and Slotted Plug
6 =	Omit	No Color Coded Powdercoating
	BL	Blue Powdercoat for DC Voltage
	OR	Orange Powdercoat for DC Voltage
	Y	Yellow Powdercoat for DC Voltage
	BR	Brown Powdercoat for DC Voltage
	R	Red Powdercoat for AC Voltage
	W	White Powdercoat for AC Voltage
	BK	Black Powdercoat for AC Voltage
	G	Green Powdercoat for AC Voltage
7 =	****	Modification - Please Consult the factory for additional options.

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

For further information on your individual application requirements, contact: Amphenol Corporation

North America:
Amphenol Industrial Operations
180 N. Freeport Drive, Plant 4
Nogales, AZ 85621
Tel: (520) 285-5130
Fax: (520) 285-5134

Email: rpedrazzini@amphenol-aio.com

Europe:
Amphenol Industrial Operations Europe
Via Barbaiana 5
1-20020 Lainate (MI) Italy
Tel: +39 02 93254.204
Fax: +39 02 93254.444

Email: info@amphenol-aio.com

Middle East:
Amphenol Middle East Enterprises FZE
Office C-37 PO Box 21107
Ajman Free Zone, UAE
Tel: +9716-7422494
Fax: +9716-7422941

Email: ameeffe@eim.ae

Asia:
Amphenol Technology Shenzhen Ltd
Block 5 Fuan 2nd Industrial Park
Dayang Rd, Fuyong Baoan
Baoan, Shenzhen, China 518103
Tel: +86 755 2881 8389
Fax: +86 755 2991 8310
Email: yb.zhu@amphenol-industrial.com