

CONEC NEWS FLASH

New Information from CONEC

CONEC—NEW Full Metal
(Nickel plated Zinc Die Cast)
bayonet style IP67 RJ45 & USB



Full Metal Bayonet Style IP67 RJ45 and USB



PDF data sheets available
upon request. Contact
Technical Support



Features and Benefits

- IP67 in mated condition—potted versions available for additional Ingress Protection.
- Meets EIA/TIA-568-B.2 Cat. 5e Specification
- Quick lock and release bayonet style interface IAW IEC-61076-3-106. Also available with M28 screw type.
- Protective Caps with lanyards
- IDC and PCB termination
- Patch cables in 2, 4 & 5 meter lengths—consult Conec for special lengths
- RoHS and REACH compliant

Applications

- Industrial Machinery
- CNC Machines
- Communication Equipment
- Food and Chemical Process Equipment
- Railway Network Systems
- Oil Exploration
- Industrial Process Control
- Diagnostic Equipment
- Printers, Display
- Factory Automation, Robotics
- Outdoor Telecom Systems
- Entertainment Systems

American CONEC
343 Technology Drive
Garner, NC 27527 USA
Tel. 919-460-8800 | Fax. 919-460-0141
www.conec.com | [technical support](#)

CONEC[®]
TECHNOLOGY IN CONNECTORS[™]