

Han-INOX[®] 3 A right angled housings and covers



Why did HARTING create the Han-INOX[®] right angled housings and covers?

HARTING created the Han-INOX[®] to address the need for stainless steel hoods and housings for the following industrial fields of application:

- **Food and Beverage**
- **Water and Sewage Treatment**
- **Pharmaceutical**
- **Chemical**
- **Offshore and Shipbuilding**
- **Mining**

The first member of the Han-INOX[®] family accepted Han[®] 10 B sized inserts and Han-Modular[®] 10 B sized frames. The initial offering was followed by 3 A sized straight hoods and bulkhead housings. The 3 A form factor has many inserts for both power and signal and is well suited to a wide variety of electronic and electrical applications.

Key Features and Benefits

- 304 stainless steel hood and housing construction is resistant to aggressive cleaning agents
- Stainless locking elements are corrosion resistant
- IP 65/67 environmental ratings suitable for wash down applications
- New covers allow easy cleaning of disconnected equipment
- Right angle cable entries suited to a variety of applications
- Smooth surface makes cleaning easy

Availability Status

All parts are now stocked in Elgin, IL and at our factory

List Prices

HARTING Part Number	Description	List SP
19 44 003 1640	Side entry hood - M20	\$73.99
19 44 003 1643	Side entry hood with glued gasket M20	\$76.44
19 44 003 0801	Right angled bulkhead mounted housing	\$72.52
19 44 003 1250	Right angled surface mounted housing M20	\$80.85
19 44 003 5426	Cover for housings for male inserts	\$44.10
19 44 003 5425	Cover for housings for female inserts	\$47.04
19 44 003 5422	Cover for hoods for male inserts	\$43.12
19 44 003 5421	Cover for hoods for female inserts	\$54.88