

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-50-0008](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: [KK® Crimp Terminal 8818, 18-22 AWG, Reel, Brass Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-08-50 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	8818
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnection System
Product Name	KK®
UPC	800753617889

Physical


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.180/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.41mm max.
Wire Size AWG	18, 20, 22
Wire Size mm²	N/A

Material Info

Old Part Number 8818-(P909)

Reference - Drawing Numbers

Product Specification	PS-08-50
Sales Drawing	SD-8818



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[8818Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac™ Applicator	0638881100
Hand Crimper	0638117500