

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-93-0200

Status:

Active

Overview:

KK® Interconnection System

Description:

3.96mm Pitch KK® Crimp Terminal Housing, Friction Ramp, 2 Circuits, Glow Wire Compatible

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0087 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Crimp Housings

3069

Power, Wire-to-Board

This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695- 2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

KK® Interconnection System

KK®

883906174194

Overview

Product Name

UPC

Physical

Circuits (maximum)

Circuits Detail

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Temperature Range - Operating

2

2

Black

94V-2

Female

Yes

Yes

Nylon

0.561/g

1

Bag

No

3.96mm

0°C to +75°C

Material Info



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
3069Series

Mates With
2220 , 3190 , 3192 , 3243, 3246, A4042, 41661 , 41662 , 41671 , 41672 , 41681 , 41682 , 41701 , 41711 , 41721 , 41741 , 41761 , 41771 , 41772 , 41791 , 41792 , 42441 , 42461 , 42471 , 42491

Use With
2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

Old Part Number	3069-G02
Reference - Drawing Numbers	
Product Specification	PS-99020-0087
Sales Drawing	SD-3069-GN***

This document was generated on 10/05/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION