

## MINI-BAT/12DC/2.6AH

Order No.: 2866569



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2866569>

Rechargeable battery module, 12 V DC, 2,6 Ah, for use with DC-UPS/4A

### Commercial data

EAN	4046356476485
Pack	1 pcs.
Weight/Piece	2.1371 KG
Catalog page information	Page 592 (IF-2009)

<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### Input data

Nominal input voltage	12 V DC
Current consumption	1 A (charging process)
Buffer period	(See the selection diagram)

#### Output data

Nominal output voltage	12 V DC
Output current	max. 15 A
Connection in series	No
Output fuse	25 A

#### General data

Width	52 mm
Height	130 mm

Depth	110 mm
Weight	1.7 kg
Degree of protection	IP20
Class of protection	III
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C

#### Accessories

Item	Designation	Description
<b>Fuse</b>		
0913757	SI FORM C 25 A DIN 72581	Fuse modular terminal block, Nominal current: 25 A, Length: 19 mm, Width: 5 mm, Height: 13 mm, Color: white

**Address**

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 00  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



© 2009 Phoenix Contact  
Technical modifications reserved;