



July 2010

STEP Power

12 and 24 V DC variant additions

Three new STEP power supplies are now available from Phoenix Contact. The new variants are 24 V DC/0.5 A, 12 V DC/1 A and 12 V DC/1.5 A (with a smaller housing).

Features

- Worldwide input voltage range
 - 85-264 V AC
 - 95-250 V DC
- Efficiency
 - Only 0.4 W consumption idling (12 V/1 A)
 - Only 0.4 W consumption idling (12 V/1.5 A)
 - Only 0.3 W consumption idling (24 V/0.5 A)
- Local diagnostics
 - Indication of the DC output status



Opportunities/applications

These new power supplies fill needs in applications with low current requirements or in low-profile control cabinets. The 12 V DC/1.5A FL power supply is just 43 mm deep, an 18 mm reduction from the other STEP power supplies.

- Building and home automation
- HVAC
- Security systems
- General low power applications

Sales tools

- Samples

Ordering information

Part Number	Description	List Price
2868596	STEP-PS/1AC/24DC/0.5A	\$39.78
2868538	STEP-PS/1AC/12DC/1	\$40.21
2868554	STEP-PS/1AC/12DC/1.5/FL	\$46.81