



## PRODUCT BRIEF

### EPCOS SAW Filter Kit

SAW Filters and Resonators for Automotive RKE and TPMS

Center Frequency 315MHz up to 868MHz

| Kit: <a href="#">B39000Z3410A003</a><br>Kit Contents: | Data Sheet Link           | Center Frequency (MHz) | Usable Bandwidth (MHz) | Typical Insertion Loss (dB) | Source/Load Impedance ( $\Omega$ ) |
|-------------------------------------------------------|---------------------------|------------------------|------------------------|-----------------------------|------------------------------------|
| <a href="#">B39321B3722U410</a>                       | <a href="#">DataSheet</a> | 315.0                  | 1.0                    | 1.4                         | 50                                 |
| <a href="#">B39321B3741H110</a>                       | <a href="#">DataSheet</a> | 315.0                  | 0.5                    | 2.1                         | 50                                 |
| <a href="#">B39321B3961B210</a>                       | <a href="#">DataSheet</a> | 315.0                  | 0.3                    | 2.1                         | 50                                 |
| <a href="#">B39321R0961H110</a>                       | <a href="#">DataSheet</a> | 315.0                  | 0.1                    | 1.4                         | 50                                 |
| <a href="#">B39431B3721U410</a>                       | <a href="#">DataSheet</a> | 433.92                 | 1.5                    | 2.6                         | 50                                 |
| <a href="#">B39431B3743H110</a>                       | <a href="#">DataSheet</a> | 433.92                 | 0.5                    | 1.9                         | 50                                 |
| <a href="#">B39431B3790Z810</a>                       | <a href="#">DataSheet</a> | 433.92                 | 0.16                   | 3.6                         | 50                                 |
| <a href="#">B39431B3960B210</a>                       | <a href="#">DataSheet</a> | 433.92                 | 0.3                    | 2.3                         | 50                                 |
| <a href="#">B39431R0960H110</a>                       | <a href="#">DataSheet</a> | 433.92                 | 0.1                    | 1.3                         | 50                                 |
| <a href="#">B39431R0990H110</a>                       | <a href="#">DataSheet</a> | 433.92                 | 0.5                    | 1.5                         | 50                                 |
| <a href="#">B39871B3744H110</a>                       | <a href="#">DataSheet</a> | 868.3                  | 0.4                    | 3.0                         | 50                                 |
| <a href="#">B39871B3725U410</a>                       | <a href="#">DataSheet</a> | 869.0                  | 2.0                    | 2.5                         | 50                                 |

**Buy Kit**

[View Kit Contents](#)

Learn More About [EPCOS Design Engineering Sample Kits](#)