



Stamped and formed contacts with selective plating

**A unique contact technology
which provides cost containment benefits without sacrificing performance.**

**Gold over nickel plating only on
active area**



Less sensitive to gold price

**No impact to electrical
performance**



Exceptional contact performance
maintained

**Selective plating is available for
both female and male contacts
from wire size 30 AWG to 14 AWG**



A full contact range

Available on a reel



Suitable for automatic crimping

Trim Trio #16 contacts

Plating information



Ordering information

Contact type	AWG	Part number				Max wire diam.	Max insulator diam.
		Male		Female			
		Standard plating	Selective plating	Standard plating	Selective plating		
Stamped & formed	14	SC14M1S6	SC14M1S18	SC14M1D70	SC14M1S31	0.125"	No insulation grip
	14	SC14ML1S6	SC14ML1S18	SC14ML1D70	SC14ML1S31	0.125"	No insulation grip
	18-16	SC16M1S6	SC16M1S18	SC16M1D70	SC16M1S31	0.078"-0.118"	Insulation grip
	18-16	SC16M1S6	SC16M1S18	SC16M1D70	SC16M1S31	0.118"	No insulation grip
	18-16	SC16ML1S6	SC16ML1S18	SC16ML1D70	SC16ML1S31	0.078"-0.118"	Insulation grip
	18-16	SC16ML1S6	SC16ML1S18	SC16ML1D70	SC16ML1S31	0.118"	No insulation grip
	22-20	SC20M1S6	SC20M1S18	SC20M1D70	SC20M1S31	0.046"-0.081"	Insulation grip
	22-20	SC20ML1S6	SC20ML1S18	SC20ML1D70	SC20ML1S31	0.046"-0.081"	Insulation grip
	26-24	SC24M1S6	SC24M1S18	SC24M1D70	SC24M1S31	0.035"-0.050"	Insulation grip
	26-24	SC24ML1S6	SC24ML1S18	SC24ML1D70	SC24ML1S31	0.035"-0.050"	Insulation grip
	14	SM14M1D70	SM14M1S31	SM14M1D70	SM14M1S31	0.125"	No insulation grip
	14	SM14ML1D70	SM14ML1S31	SM14ML1D70	SM14ML1S31	0.125"	No insulation grip
	18-16	SM16M1D70	SM16M1S31	SM16M1D70	SM16M1S31	0.078"-0.118"	Insulation grip
	18-16	SM16M1D70	SM16M1S31	SM16M1D70	SM16M1S31	0.118"	No insulation grip
	18-16	SM16ML1D70	SM16ML1S31	SM16ML1D70	SM16ML1S31	0.078"-0.118"	Insulation grip
	18-16	SM16ML1D70	SM16ML1S31	SM16ML1D70	SM16ML1S31	0.118"	No insulation grip
	22-20	SM20M1D70	SM20M1S31	SM20M1D70	SM20M1S31	0.046"-0.081"	Insulation grip
	22-20	SM20ML1D70	SM20ML1S31	SM20ML1D70	SM20ML1S31	0.046"-0.081"	Insulation grip
	26-24	SM24M1D70	SM24M1S31	SM24M1D70	SM24M1S31	0.035"-0.050"	Insulation grip
	26-24	SM24ML1D70	SM24ML1S31	SM24ML1D70	SM24ML1S31	0.035"-0.050"	Insulation grip

Packaging

Conscious of the wide variety of applications, contact packaging is available for both small series (bulk packaging) and high volume production (reeled contacts):

Size contact #16



• 25 pieces bulk packaging



• 3000 pieces reeled

For further information, visit our website www.souriau-industrial.com
or contact us at technicalsupport@souriau.com