

1P - 2T





示意图 SCHEMATIC



安装孔 PIERCING PLAN

规格 Specifications

额定负荷 Ratings	DC 30 V 0.3 A
初瞬接触电阻 Initial Contact Resistance	30 mΩ Max.
绝缘电阻 Insulation Resistance	DC 500 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric	AC 500 V (50~60HZ) 60 Sec.

操作力 Operating Force (gf)	A → B
	200 ± 100
负荷寿命 Operating Life With Load	10,000 次 Cycles

6	弹簧 SPRING	STEEL	1	NATURAL
5	端子 TERMINAL	C2680R ①	3	Ag PLATED
4	基板 TERMINAL BASE	PHENOL RESIN	1	YELLOW
3	接触片 CONTACT	COPPER WIRE	1	Ag PLATED
2	胶柄 KNOB	P O M	1	G 2 - 11
1	铁壳 FRAME	S P C C	1	Ni PLATED BLACKENED

A	版本 A01 变更为 A	2006.1.29
A01	ADD: 规格 Specifications 见 ①	1/4.06
01	C2680R-EH → C2680R 见 ①	赖立辉 9 JUL 93
标号 REV	内容 DESCRIPTION	签名 SIGN. 日期 DATE

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	SLIDE SWITCH	ITEM NO	SS-12F23-G	
UNDER 1	± 0.10	DRAWN	2006-4-1	VERSION	A0+	PAGE 1 OF 1
1 - 10	± 0.30	REVIEWED	06-4-3	SCALE	A	UNIT mm
OVER 10	± 0.50	APPROVED	4/3-06	PROJECTION		

COMAX ELECTRONICS (HUIZHOU) CO., LTD.