

Test Report



Report No. A225036410210100401R1

Page 1 of 4

Company Name GLOBAL CONNECTOR TECHNOLOGY LTD
Shown on Report
Address UNIT B, 8/F, HANG CHEONG FACTORY BUILDING, 1 WING MING
STREET, CHEUNG SHA WAN, KOWLOON, HK

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the client

Sample Name SMA Bulkhead Jack with O-ring, PCB mount, Right angle
Part number RFPC-SMA41-FN
Sample Receiving State Normal
Sample Received Date May 28, 2025
Testing Period May 28, 2025-Jun. 16, 2025

**Test Requested**

No.	Test Item
1	IPX7

Test Result(s): Please see the following pages.

Approved by

Tim Sun

Date

Jun. 18, 2025

Tim Sun

Approved Signatory



No. R2082A65A2

Centre Testing International Group Co., Ltd.

Hongwei Industrial Zone, Bao'an 70 District, Shenzhen, Guangdong, China

Test Report

Report No. A225036410210100401R1

Page 2 of 4

Tested Sample(s)

Sample No.	Sample Name	Quantity
A2250364102101004	SMA Bulkhead Jack with O-ring, PCB mount, Right angle	1pc

Sample Photo(s)

A2250364102101004

Test Report

Report No. A225036410210100401R1

Page 3 of 4

Test Item: IPX7**1. Test Equipment**

Equipment Name	Model
Waterproof grade testing machine	JX1040

2. Environmental Conditions

Temperature: 24.5°C; Humidity: 55%RH

3. Test Standard: IEC 60529:2013**4. Test Condition**

The lowest point of the sample is located 1000 mm below the surface of the water.

Test duration: 30min

5. Test Result(s)

Sample No.	Criterion	Test result (Visual inspection)	Conclusion
A2250364102101004	There is no water inside the sample.	No water enters the sample	Pass

Sample Photo(s) after the test

A2250364102101004

Remark: The testing data and result(s) in this report is(are) just for scientific research, education, internal quality control and product development etc.

Test Report

Report No. A225036410210100401R1

Page 4 of 4

Note: This testing report added “Part number” based on the original report of No. A225036410210100401. This testing report displaces the original one which was invalid since the date of this testing report released.

Statement:

1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
2. Company Name and Address shown on Report, the sample(s) and sample Information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
3. The result(s) shown in this report refer(s) only to the sample(s) tested;
4. Without written approval of CTI, this report can't be reproduced except in full;
5. In case of any discrepancy between the English version and Chinese version of the testing reports(if generated), the Chinese version shall prevail.

*** End of Report ***

