



Installation Manual

Type: Adapters from 2.75W to 300W (Models: AA, AQ, MQ, PMA, PPL, PSA, PSAA, PSAC, PSAF, PSAI, PSC, PSM)

Installation

1. Before attaching the DC plug of an adapter to equipment, please unplug the adapter from the AC power and verify that the output connector, polarity, output voltage, and output current of the unit is suitable for and within the rating of the equipment.
2. Keep the linkage between the adapter and its power cord tight, as well as connecting the DC plug to the equipment properly.
3. Protect the power cord and input line against mechanical stress.
4. Ensure good ventilation for the unit during use to prevent it from overheating. A 10-15cm clearance from other heat sources must maintained.
5. An approved power cord should be greater than or equal to SVT/SPT or H03VV-F.
6. If the end equipment is not used for a long period of time, disconnect the equipment from the power supply to avoid being damaged by voltage peaks or lightning strikes.
7. For additional information about the products, please refer to www.phihong.com.

Warning / Caution

- Risk of electrical shock and energy hazards. All failures should be examined by a qualified technician. Please do not remove the case of the adapter and try to fix the issue yourself.
- Risk of fire or electrical shock. The openings should be protected from foreign objects or dripping liquids.
- Using the wrong DC plug or forcing a DC plug into an electronic device may damage the device or cause it to malfunction. Please refer to the DC plug compatibility information shown in the datasheets.
- Adapters should be placed on a reliable surface. A drop or fall could cause damage.
- Do not put adapters in places in a damp environment or near/in the water.
- Do not put adapters in places with high ambient temperature or near/in a heat source.
- Output current and output wattage must not exceed the rated values on datasheets.
- Disconnect the unit from the AC power before cleaning. Only use a slightly damp cloth to wipe the product. Do not use any liquid detergents or aerosol cleaners.
- Please contact your local qualified recycler when you want to dispose the product.
- This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:
 - a) This device may not cause harmful interference.
 - b) This device must accept any interference received, including interference that may cause undesired operation.



Sales Office Locations

Phihong Technology Co., Ltd

Headquarters
No. 568, Fusing 3rd Rd
Gueishan District
Taoyuan City (33383), Taiwan
Tel: +886-3-3277288
Fax: +886-3-3277622
phsales@phihong.com.tw
www.phihong.com.tw

Phihong China

Science & Technology Rd.,
Silver Lake Industrial Area Qingxi Town,
Dong Guan City, Guang Dong (523648),
China
Tel: +86-769-87319026
Fax: +86-769-87317106
phsales@phihong.com.tw
www.phihong.com.tw

Phihong USA

Corporate Office
47800 Fremont Blvd.
Fremont, CA94538, USA
Tel: +1-510-445-0100
Fax: +1-510-445-1678
usasales@phihongusa.com
www.phihong.com

Phihong Europe

Wattstraat 50
2171 TR Sassenheim
The Netherlands
Tel: +31-(0)-252-225910
Fax: +31-(0)-252-218764
sales@phihong.eu
www.phihong.com