

6

5

4

3

2

1

D

D

C


C

B






B

A

A



14.80 [.583] 7.00 [.276]

KITTED WITH ONE ALIGNMENT INSERT
AND ONE INSTRUCTION LABEL

PANEL CUTOUT

NOTES:

- MATERIALS AND FINISHES:
INSULATOR AND ALIGNMENT INSERT: GLASS-FILLED NYLON, UL 94V-0, COLOR: ORANGE.
FLOAT BUSHINGS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
SCREWS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
- DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST GOLDFISH PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM.
- CONNECTORS ARE COMPLIANT TO THE CURRENT RoHS DIRECTIVE.

BY SB		CHK AP	3RD ANGLE		POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.		 Positronic® CONNECTPOSITRONIC.COM
APR SS		RELEASED DATE: 2024-10-19					
TOLERANCES			SCALE				
±0.03mm [.001 INCHES] FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES] FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES] FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES] FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]			NTS				
			PART NUMBER		GFSH89M182/AA		SERIES
					GFSH89M182/AA		GFSH
			TITLE				
			CREATED ON: 2024-10-19		SHEET SHEET 1 OF 1		REV A