

Kitting Order Description: Res Kit CFR25RS 5% (86 VALUES)

Part Number : 1625873-8

Quantity per Value: 20 pcs

Style: ALBUM KIT



Page: 1 of 1

No.	Value	Alias	TCPN	No.	Value	Alias	TCPN
1	1R0	CFR25J1R0	4-1623930-1	44	3K3	CFR25J3K3	2-1623931-1
2	1R2	CFR25J1R2	4-1623930-2	45	3K9	CFR25J3K9	2-1623931-3
3	1R5	CFR25J1R5	4-1623930-5	46	4K7	CFR25J4K7	3-1623931-8
4	1R8	CFR25J1R8	4-1623930-7	47	5K6	CFR25J5K6	5-1623931-3
5	2R2	CFR25J2R2	7-1623930-4	48	6K8	CFR25J6K8	6-1623931-6
6	2R7	CFR25J2R7	7-1623930-5	49	8K2	CFR25J8K2	8-1623931-1
7	3R3	CFR25J3R3	2-1623931-7	50	10K	CFR25J10K	1623930-3
8	3R9	CFR25J3R9	2-1623931-9	51	12K	CFR25J12K	1-1623930-1
9	4R7	CFR25J4R7	4-1623931-1	52	15K	CFR25J15K	2-1623930-0
10	5R6	CFR25J5R6	5-1623931-6	53	18K	CFR25J18K	2-1623930-7
11	6R8	CFR25J6R8	6-1623931-8	54	22K	CFR25J22K	5-1623930-5
12	8R2	CFR25J8R2	8-1623931-4	55	27K	CFR25J27K	6-1623930-3
13	10R	CFR25J10R	1623930-5	56	33K	CFR25J33K	1623931-8
14	12R	CFR25J12R	1-1623930-2	57	39K	CFR25J39K	1-1623931-8
15	15R	CFR25J15R	2-1623930-1	58	47K	CFR25J47K	3-1623931-5
16	18R	CFR25J18R	2-1623930-8	59	56K	CFR25J56K	4-1623931-8
17	22R	CFR25J22R	5-1623930-6	60	68K	CFR25J68K	6-1623931-3
18	27R	CFR25J27R	6-1623930-4	61	82K	CFR25J82K	7-1623931-8
19	33R	CFR25J33R	1623931-9	62	100K	CFR25J100K	1623930-1
20	39R	CFR25J39R	1-1623931-9	63	120K	CFR25J120K	1623930-9
21	47R	CFR25J47R	3-1623931-7	64	150K	CFR25J150K	1-1623930-7
22	56R	CFR25J56R	4-1623931-9	65	180K	CFR25J180K	2-1623930-5
23	68R	CFR25J68R	6-1623931-4	66	220K	CFR25J220K	5-1623930-2
24	75R	CFR25J75R	7-1623931-4	67	270K	CFR25J270K	6-1623930-0
25	82R	CFR25J82R	7-1623931-9	68	330K	CFR25J330K	1623931-5
26	100R	CFR25J100R	1623930-2	69	390K	CFR25J390K	1-1623931-5
27	120R	CFR25J120R	1-1623930-0	70	470K	CFR25J470K	3-1623931-3
28	150R	CFR25J150R	1-1623930-8	71	560K	CFR25J560K	4-1623931-6
29	180R	CFR25J180R	2-1623930-6	72	680K	CFR25J680K	6-1623931-1
30	220R	CFR25J220R	5-1623930-4	73	820K	CFR25J820K	7-1623931-6
31	270R	CFR25J270R	6-1623930-2	74	1M0	CFR25J1M0	3-1623930-5
32	330R	CFR25J330R	1623931-7	75	1M2	CFR25J1M2	3-1623930-6
33	390R	CFR25J390R	1-1623931-6	76	1M5	CFR25J1M5	3-1623930-8
34	470R	CFR25J470R	3-1623931-4	77	1M8	CFR25J1M8	4-1623930-0
35	560R	CFR25J560R	4-1623931-7	78	2M2	CFR25J2M2	7-1623930-0
36	680R	CFR25J680R	6-1623931-2	79	2M7	CFR25J2M7	7-1623930-2
37	820R	CFR25J820R	7-1623931-7	80	3M3	CFR25J3M3	2-1623931-4
38	1K0	CFR25J1K0	2-1623930-9	81	3M9	CFR25J3M9	2-1623931-5
39	1K2	CFR25J1K2	3-1623930-1	82	4M7	CFR25J4M7	4-1623931-0
40	1K5	CFR25J1K5	3-1623930-3	83	5M6	CFR25J5M6	5-1623931-4
41	1K8	CFR25J1K8	3-1623930-4	84	6M8	CFR25J6M8	6-1623931-7
42	2K2	CFR25J2K2	6-1623930-6	85	8M2	CFR25J8M2	8-1623931-2
43	2K7	CFR25J2K7	6-1623930-8	86	10M	CFR25J10M	1623930-4