

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0579649702

Status:

Active

Description:

1.52mm OBD-II Male Terminal for AVS(CAVS) 0.3-0.5

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-57964-001-001 (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Product Name

UPC

Crimp Terminals

57964

Power, Wire-to-Wire

Yes

OBD-II

756054300091

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Male

Brass

Tin

Tin

0.306/g

Reel

Crimp or Compression

1.60-1.40mm

20, 22

0.30-0.50

Material Info

Reference - Drawing Numbers

Crimp Specification

Packaging Specification

CS-57964-001-002

PK-57964-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

57964 Series

Use With

685031602

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for MTC (Multi Terminal Connector) Female Terminal, 14-18 AWG	638138600
Hand Crimp Tool for OBD II 1.52mm Crimp Terminal, 0.30-0.50mm² and 20-22 AWG	638194700

FineAdjust Applicator 639011200
for 1.52mm Female
Terminal
T2 Terminator for 639111200
OBD II 1.52mm
Crimp Terminal for
20-22 AWG

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION