


PHYSICAL

Conductors: 26 AWG 7/34 Tinned Copper
 Insulation: .010" Nom. PVC
 Color Code: Red, White, Black
 Temp. Rating: 80°C

ELECTRICAL

Voltage Rating: 300 V
 Current Rating: 1.6 A @ 10°C Rise Above Ambient
 Insulation Res.: 10¹⁰ ohms – 10 ft Min.
 Cable Style: UL AWM Style 2697 (80°C, 300V)



DRAWN	PROD ENG	QA	MKT	P/ECN#	DRAWING NO. 111-2699-988	AMPHENOL SPECTRA-STRIP 720 SHERMAN AVE TEL (203) 281-3200 HAMDEN CT 06514 FAX (203) 281-5872	Rev -
5/15/98					TITLE: Spectra-Bond® Parallel Conductor Cable		SHEET 1 of 1