



Rating	3A 125V, 1.5A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P SPST OFF-(ON)(LED)		


LED Rating:
Red: If=20 mA, Vf=2 V

Material:

Frame: Nylon 66+33%GF, Black

Actuator: PC, Red

Printed: None



Tolerances ± 0.3 Unless Otherwise Specified

07/26/11	雷云飛	Update the drawing layout			△	
Date	Name	Description			No.	
Drawn	Checked	Approved	SCI BOM No.	Model Name	PUSH SWITCH	
雷云飛	符明達	符明達	Customer No.	Model No.	R13-508AL-05	Rev.
07/26/11	8/12/11	8/12/11	Unit	mm	Shin Chin Industrial Co., Ltd.	
						1

同規格 R13-11