


- Notes:**
- Material and Finish:
 - Coupler Ring: Polyester (Black); UL94 V-0
 - Plug Housing: Polyester (Black); UL94 V-0
 - Cable Gland: PA (Black), UL94 V-0
 - Cable Gland Rubber Ring: NBR, Color: Black
 - Cable Fitting: PA (Black), UL94 V-0
 - Interfacial Seal: Silicon, Color: White
 - Protective Cap: Polyester (Black); UL94 V-0
 - Tether: Polycarbonate (Black)
 - Duplex LC Connector
 - Housing: PEI, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green**
 - Inner Sub Assembly: Zirconia, Metal and PTFE
 - Crimp Barrel: Brass, Nickel Plated
 - Ferrule: Brass, Nickel Plated
 - Dust Cap: PC, Color: White
 - Duplex LC Clip: PC, Color: Black
 - Operating Temperature: -40~C to +85~C
 - IP67 rated when covered or fully mated with the appropriate mating connector
 - Accept 4.5mm to 8.0mm outside diameter fiber optic cable

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Plastic Duplex LC Single Mode Plug Kit + Plug Cover Assembly	17-300200
Plastic Duplex LC Multi Mode Plug Kit + Plug Cover Assembly	17-300210
Plastic Duplex LC APC Single Mode Plug Kit + Plug Cover Assembly	17-300220

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.30 1 PLC ±0.20 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±1°		 Autodesk Inventor	Scale: NTS	Dim. in mm				
							Material: See Notes					
	Name			Title			Approval Date			Title: IP67 Industrial Duplex LC Plug + Protective Cover Assembly Kit Plastic Version		
										Drawing No.: 17K1A216 Part No.: SEE P/N ABOVE		
									DIN A3			
									Sheet 1/1			

CONEC

DIN
A3
Sheet
1/1