




注 記 NOTES

- △1 偶数極品に適用。
APPLIES ONLY TO EVEN NO. CKT. SIZES.
2. 嵌合相手：51103 シリーズ
MATES WITH: 51103 SERIES.
- △3 累積ピッチの許容差は、20ピッチで ±1.0mm とする。
ACCUMULATED TOLERANCE IS TO BE ±1.0mm PER 20 PITCH.
- △4 粘着テープは台紙からはみ出さない事。
THE ADHESIVE TAPE SHOULD NOT BE PROTRUDED FROM THE BASE TAPE.
- △5 リード線の曲がりの許容差は 1mm MAX. とする。
CAMBER OF THE LEADS : 1mm MAX.
- △6 測定位置は、コネクタの先端とする。
INCLINED POSITION FROM THE CENTER-LINE, SHOULD BE 1mm MAX. MEASURING SHOULD BE DONE, USING THE TOP OF BASE TAPE AS DATUM.
- △7 測定値は台紙の上端とし、リード線との間隔とする。
DIM. 3.85 AND DIM. 5 SHOULD BE MEASURED ON THE TOP OF BASE TAPE. DIMENSIONS ARE A SPACING BETWEEN THE CENTER-LINES.
8. 製品番号の下 1 桁は色を表します。
LAST DIGIT OF PART NUMBER INDICATES COLOR.
- | | | | | | | | | |
|---|-----|--------|---|-----|-------|---|-----|-------|
| 0 | : 白 | WHITE | 1 | : 黒 | BLACK | 2 | : 赤 | RED |
| 3 | : 黄 | YELLOW | 4 | : 青 | BLUE | 6 | : 緑 | GREEN |

400	9.95	25.4	22.4	20.7	17.5	53375-089*	8
	7.45	↑	19.9	18.2	15	↑ -079*	7
	7.45	↓	17.4	15.7	12.5	↑ -069*	6
500	4.95	↓	14.9	13.2	10	↑ -059*	5
	4.95	25.4	12.4	10.7	7.5	↓ -049*	4
900	2.45	12.7	9.9	8.2	5	↓ -039*	3
	2.45	12.7	7.4	5.7	2.5	53375-029*	2
包装数量/箱 QTY/CARTON	E	D	C	B	A	MATERIAL NO. MODEL NO. 53375-**9*	極数 NO. OF CKTS.

GENERAL TOLERANCES (UNLESS SPECIFIED)				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				CURRENT REV DESC: OBSOLETE PART NO			
DIMENSION UNITS				SCALE		molex 2.5 WIRE TO BOARD CONN. WAFER ASSY RADIAL TAPING -LEAD FREE-					
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 629832		DRWN: VLOKESHA 2019/12/16 CHK'D: GGA 2020/01/22 APPR: GGA 2020/01/22					
						INITIAL REVISION: DRWN: M.UMEDA 2005/01/21 APPR: N.UKITA 2005/01/21					
						THIRD ANGLE PROJECTION DRAWING SERIES A3-SIZE 53375					
						MATERIAL NUMBER CUSTOMER SEE TABLE GENERAL MARKET					
						SHEET NUMBER 1 OF 3					

