
HEYCO




HEYClip™ Nylon Wire Clips


Adhesive-Backed

MAXIMUM BUNDLE DIAMETER		RATED STATIC LOAD	PART NO. Adhesive			DESCRIPTION	FOOTPRINT A x B		OVERALL HEIGHT C		CLAMP WIDTH D	
			Standard		Super							
in.	mm.	lb.	Gray	Black	Gray		in.	mm.	in.	mm.	in.	mm.
.187	4,7	1/2	**3857**	**3917**	-	WCA 187-500	.74 x .62	18,8 x 15,7	.34	8,6	.39	9,9
.250	6,4	3/4	**3858**	**3918**	**3858A**	WCA 250-750	1.00 x .87	25,4 x 22,1	.42	10,7	.63	16,0
.375	9,5	1	**3859**	**3919**	**3859A**	WCA 375-1000	1.00 x 1.00	25,4 x 25,4	.50	12,7		
.500	12,7	1-1/4	**3860**	**3920**	**3860A**	WCA 500-1250	1.00 x 1.21	25,4 x 30,7	.68	17,3	.64	16,3
.750	19,1	1-3/4	**3861**	**3921**	-	WCA 750-1750	1.15 x 1.45	29,2 x 36,8	.99	25,1		
1.000	25,4	4	**3867**	**3923**	-	WCA1000-4000	1.98 x 2.24	50,3 x 56,9	1.37	34,8	1.26	32,0
1.500	38,1	6	**3868**	**3930**	-	WCA 1500-6000	2.42 x 2.95	61,5 x 74,9	1.77	45,0	1.31	33,3

Standard color gray or black. Super duty adhesive backing available as shown.

- Releasable and reusable clips for easy wire bundle routing.
- Quick and easy installation–simply peel off backing and press into place.
- Made of Nylon 6/6 with a 94V-2 flammability rating.
- Seven sizes for bundles from .187˝ (4,7 mm) to 1.500˝ (38,1 mm) in diameter.
- Apply to a clean, dry surface.
- Three sizes in Super Adhesive Gray.
- Super adhesive temperature range is -40°F (-40°C) to 250°F (121°C).









HEYClip™ Installation Instructions


Adhesive-Backed Wire Clips



HEYClip attaches easily to any commercial surface. Backing strips off easily.



Unique closure operates easily, locks securely. When closed, HEYClip will not release until push tab is released.



HEYClip opens easily to permit removal of bundle.

Material	**Nylon 6/6**
Flammability Rating	**94V-2**
Temperature Range	**-20°F (-29°C) to 150°F (66°C)**
Recommended Storage Temperature	**From 60°F (16°C) to 80°F (27°C) with approximate relative humidity of 50%**
Rated Static Loads	**Pertain to parts fastened to a flat, clean, and dry surface**

Quick Specs