





Heyco® Nylon PCB Supports

Locking Reverse PCB Supports

PANEL DIMENSIONS				PCB DIMENSIONS				PART NO.	DESCRIPTION	PART DIMENSIONS					
Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter				A Spacing		B Head Length		C Foot Length	
in. mm.		in. mm.		in. mm.		in. mm.				in. mm.		in. mm.		in. mm.	
SS LR Series															
.06	1,6	.187	4,8	.06	1,6	.125	3,2	3699	SS LR 5/16	.31	7,9				
								3700	SS LR 3/8	.38	9,5	.06	1,5	.19	4,8
								3701	SS LR 7/16	.44	11,1				

Standard color natural.



Stacking Retainer Supports

PANEL DIMENSIONS				PCB DIMENSIONS				PART NO.	DESCRIPTION	PART DIMENSIONS					
Maximum Thickness		Mounting Hole Diameter		Screw Size	Maximum Thickness		A Spacing			B Outside Diameter		C Inside Diameter			
in.	mm.	in.	mm.		in.	mm.	in.			mm.	in.	mm.	in.	mm.	
SS RS Series															
.06	1,6	.187	4,8	#4	.06	1,6	3681	HSSRS4-02	.13	3,2	.26	6,6	.13	3,2	
							3683	HSSRS4-03	.19	4,8					
							3684	HSSRS4-04	.25	6,4					
							3685	HSSRS4-06	.38	9,5					
							3687	HSSRS4-08	.50	12,7					
							3688	HSSRS4-10	.63	15,9					
		.234	6,0	#6	.06	1,6	3689	HSSRS6-04	.25	6,4	.31	7,9	.15	3,9	
							3690	HSSRS6-06	.38	9,5					
							3691	HSSRS6-08	.50	12,7					
							3692	HSSRS6-10	.63	15,9					
				#8	.06	1,6	3693	HSSRS8-04	.25	6,4	.31	7,9	.17	4,3	
							3694	HSSRS8-06	.38	9,5					
							3695	HSSRS8-08	.50	12,7					
							3696	HSSRS8-10	.63	15,9					

Standard color natural.

- Durable, lightweight, and high strength design.
- Locking Reverse PCB Supports are **ideal for minimal clearance locations** and suitable for chassis-to-board requirements.



- Stacking Retainer Supports are suitable for **board to board and chassis to board** requirements.
- Easily installed without tools.

Material: Nylon 6/6
 Flammability Rating: 94-V0
 Temperature Range: 32°F (0°C) to 185°F (85°C)

Quick Specs