



8400 Series Tubeaxial

**Brushless DC, plastic housing, plastic
impeller. Air exhaust over struts.
UL, CSA, VDE approvals.**

Part Number	CFM @ 0	Curve	Volts	Voltage Range	Power (W)	dBA	Max Ambient Temp C	Wgt. (lbs)	Type Of Bearing	Features	Size
8414GL	21	1	24	12 to 28	0.8	20	75	0.31	Sintec	Leads	80x80x25 mm
8414L	21	1	24	12 to 28	0.8	21	75	0.31	Ball	Leads	80x80x25 mm
8412GL	21	1	12	7 to 15	0.8	20	75	0.31	Sintec	Leads	80x80x25 mm
8412L	21	1	12	7 to 15	0.8	21	75	0.31	Ball	Leads	80x80x25 mm
8414GM	27	2	24	12 to 28	1.2	29	75	0.31	Sintec	Leads	80x80x25 mm
8414M	27	2	24	12 to 28	1.4	29	75	0.31	Ball	Leads	80x80x25 mm
8412GM	27	2	12	7 to 15	1.2	29	75	0.31	Sintec	Leads	80x80x25 mm
8412M	27	2	12	7 to 15	1.4	29	75	0.31	Ball	Leads	80x80x25 mm
8414	33	3	24	12 to 28	2.4	35	75	0.31	Ball	Leads	80x80x25 mm
8414/2	33	3	24	12 to 28	2.4	35	75	0.31	Ball	Leads	80x80x25 mm
8414G	33	3	24	12 to 28	2.3	35	75	0.31	Sintec	Leads	80x80x25 mm
8412	33	3	12	7 to 15	2.4	35	75	0.31	Ball	Leads	80x80x25 mm
8412/12	33	3	12	7 to 15	2.4	35	75	0.31	Ball	Leads	80x80x25 mm
8412/2	33	3	12	7 to 15	2.4	35	75	0.31	Ball	Leads	80x80x25 mm
8412G	33	3	12	7 to 15	2.3	35	75	0.31	Sintec	Leads	80x80x25 mm

