

HINGE LOCATION

		531-40051
531-40118	531-40047-3	531-40065
31-71013-RFX	903-512J-71P	919-132J-71PT
31-71014-RFX	903-517P-71A	919-136P-71AX

LAYOUT FOR CONNECTORS IN SAMPLE BOX 999-686

Amphenol RF
Danbury, CT, USA
Tainan, Taiwan
Shenzen, China
www.amphenolrf.com

					APPROVAL	DATE	THIS DRAWING CONTAINS INFORMATION WHICH IS THE PROPRIETARY PROPERTY OF AMPHENOL CORPORATION. THIS DRAWING IS CONFIDENTIAL AND ITS CONTENTS MAY NOT BE DISCLOSED WITHOUT THE PRIOR WRITTEN CONSENT OF AMPHENOL CORPORATION.	TITLE: BROARDBAND SAMPLE KIT	CODE ID: 74868	www.amphenolrf.com
A	RELEASE TO MFG	02/16/2005	45362	DRAWN BY	C. McGRATH	12/03/2004			SCALE: NONE	SHEET: 1 of 2
REV	DESCRIPTION	DATE	ECO	ENGINEER	O. BARTHELMES	12/03/2004		Drawing No.	Rev	
REVISIONS				MANAGER	O. BARTHELMES	02/16/2005	REFERENCE: EAR 1599	CAD FILE: I:\HARD\999-680	999-680	A

NOTES:
1. ARTWORK DETAILS FOR INDIVIDUAL LABELS TO BE SUPPLIED BY MARCOM.

919-136P-71AX	13	1	MCX R/A (M) CRIMP	
919-132J-71PT	12	1	MCX SURFACE MOUNT PC RECEPT	
903-517P-71A	11	1	SMB (M) R/A	
903-512J-71P	10	1	SMB (F) PC MOUNT	
31-71014-RFX	9	1	BNC (F) CRIMP	
31-71013-RFX	8	1	BNC (M) CRIMP	
531-40065	7	1	PANEL MOUNT 'G' CONNECTOR	
531-40051	6	1	G' (F) PCB MOUNT	
531-40047-3	5	1	F' (F) PCB R/A	
531-40118	4	1	BULKHEAD ADAPT 'F'(F) TO 'G'(M)	
999-686	3	1	BOX	
999-687	2	1	INSIDE LABEL	
999-681	1	1	OUTSIDE LABEL	
AMPHENOL P/N	ITEM	QTY	DESCRIPTION	OTHER P/N

Amphenol RF
Danbury, CT, USA
Tainan, Taiwan
Shenzen, China
www.amphenolrf.com

					APPROVAL	DATE	THIS DRAWING CONTAINS INFORMATION WHICH IS THE PROPRIETARY PROPERTY OF AMPHENOL CORPORATION. THIS DRAWING IS CONFIDENTIAL AND ITS CONTENTS MAY NOT BE DISCLOSED WITHOUT THE PRIOR WRITTEN CONSENT OF AMPHENOL CORPORATION.	TITLE: BROADBAND SAMPLE KIT	CODE ID: 74868	www.amphenolrf.com	
A	RELEASE TO MFG	02/16/2005	45362	DRAWN BY	C. McGRATH	12/03/2004			SCALE: NONE	SHEET: 2 of 2	
REV	DESCRIPTION	DATE	ECO	ENGINEER	O. BARTHELMES	12/03/2004			Drawing No.		Rev
REVISIONS				MANAGER	O. BARTHELMES	02/16/2005	REFERENCE: EAR 1599		CAD FILE: I:\HARD\999-680	999-680	