

[»Back to Board Level Products](#)

575815B00000G

TO-3



Representative Photo Only

Low cost diamond shaped basket heat sink

Height: 25.40

Mount Orientation: Horizontal

Finish: Black Anodize

RoHS: compliant

Thermal Resistance: 11.00

ENTER QTY:

VIEW PRICE

Need assistance?

Call us: 1-855-32-AAVID
Email: estore@aavid.com

[» Help Page](#)

Check Distributor Stock



Enter a part number for pricing and availability.

Go

- > [Request a Sample](#)
- > [Request a Quote](#)
- > [Ask an Engineer](#)

The Fine Print

[Product Return Policy](#)
[Terms & Conditions](#)
[Privacy Policy](#)



Customer Assistance

- [Contact Us](#)
- [Find a Distributor](#)
- [Find a Sales Rep](#)
- [Request a Quote](#)
- [Get Design Assistance](#)
- [Terms and Conditions](#)
- [Returns](#)

Popular Products

- [Fans Heat Sinks](#)
- [Extrusions](#)
- [Board Level](#)
- [Liquid Cooling](#)
- [Heat Pipe Technology](#)
- [Heat Sink Accessories](#)
- [Interface Materials](#)

Our Company

- [News and Events](#)
- [Management Team](#)
- [Worldwide Locations](#)
- [Disclaimer](#)
- [Customer Survey](#)
- [Privacy Policy](#)
- [Careers](#)

Connect with Aavid

Like / Follow / Connect



© Copyright 2017 Aavid Thermalloy, LLC.

USA: 1.855.32.AAVID **Europe:** 39.051.764002 **Asia:** 86.21.6115.2000 x 8122