

Cable to Cable

.050"


9 thru 51 Contacts

Low Profile Metal

MQ

Low Profile Plastic

MP






MQ-222-031-2A3-2200
(METAL)

MP-221-031-2A3-2200
(PLASTIC)

MQ-212-031-161-41WS
(METAL)

MP-211-031-161-41WS
(PLASTIC)



DIMENSIONS								
SIZE	CONTACT ROWS	A	B		C	D	E	H
			PLUG MAX	RCPT MAX			POTTING WELL MAX	
9	2	.778	.292	.378	.398	.565	.173	.208
15		.928	.442	.528	.548	.715		
21		1.078	.592	.678	.698	.865		
25		1.178	.692	.778	.798	.965		
31		1.328	.842	.928	.948	1.115		
37		1.478	.992	1.078	1.098	1.265		
51	3	1.428	.942	1.028	1.048	1.215	.220	.250