

TMR-JSXX12-XXXXSCXXX

| KEYING OPTIONS |             |
|----------------|-------------|
| A              | LIGHT BROWN |
| B              | RED         |
| C              | BLUE        |
| D              | GREEN       |


| CONTACT FINISH |      |
|----------------|------|
| 0              | GOLD |

| TERMINATION SIZE |          |
|------------------|----------|
| 0                | STANDARD |


| INSERT CODE |                  |
|-------------|------------------|
| 005A        | 5 POSITION, STD  |
| 018A        | 18 POSITION, STD |

| HOUSING FINISH |            |
|----------------|------------|
| N              | TIN NICKEL |



| HOUSING MATERIAL |          |
|------------------|----------|
| A                | ALUMINUM |




PANEL CUTOUT




ISOMETRIC VIEW  
FOR REFERENCE ONLY  
TMR-JSAN12-018ASC00A SHOWN



KEYING OPTIONS (VIEW LOOKING AT RECEPTACLE FACE)






- NOTES:
- 1. SEE ESG6092 FOR MATERIAL AND PERFORMANCE SPECIFICATIONS
  - 2. SEE ESG6093 FOR ASSEMBLY INSTRUCTIONS
  - 3. SIZE 16 SOCKET CONTACTS PER M39029/57-358
  - 4. SIZE 22D SOCKET CONTACTS PER M39029/57-354
  - 5. SIZE 20MD SOCKET CONTACTS PER AIRBORN TMC-S20MD
  - 6. SPANNER WRENCH PART NUMBER: TMT-N0012
  - 7. TORQUE NUT TO 88.5±8 IN-LB [10±1 Nm]



|                                                                                                |                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                |                                                       |
|------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| MATERIAL: SEE NOTES<br>Temper:<br>Per Spec.:<br>R/M P/N ref: N/A<br>Certification required: NO | UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE:<br>Decimals: .XX ± 0.01      Concentricity:<br>Decimals: .XXX ± 0.008      Angles: ± 1°<br>Decimals: .XXXX ± 0.0040      Radius: ±<br>Parts are to be symmetrical about centerline within ± .005<br>Surfaces to be flat, perpendicular parallel within .004 T.I.R.<br>Dimensions are in inches/DO NOT SCALE PRINT<br>Surface finish to be $\sqrt{\text{ }}$ or better | AirBorn<br>Georgetown, Texas 78626                                                             | Cage Code<br>10400                                    |
| HEAT TREAT: SEE NOTES<br>Per Spec.:<br>Certification required: NO                              | APPLICATION: TRIMATE SERIES                                                                                                                                                                                                                                                                                                                                                                                       | DRAWING STATE: Released<br>This drawing is not authorized for production unless it is released | RECEPTACLE, SIZE 12<br>JAM NUT, IST<br>SOCKETS, CRIMP |
| FINISH: SEE NOTES<br>Per Spec.:<br>Certification required: NO                                  | REV - INITIAL RELEASE<br>CC 060923<br>CC 060923                                                                                                                                                                                                                                                                                                                                                                   | DR. CC 060923<br>TITL<br>RCS 060923                                                            | SIZE<br>C                                             |
| MAKE FROM: N/A<br>NEXT ASSY: N/A                                                               | REL. CC 060923<br>APPD. RCS 060923                                                                                                                                                                                                                                                                                                                                                                                | DWG# TMR-JSXX12-XXXXSCXXX                                                                      | REV. -<br>SHEET 1/3                                   |

TMR-JSXX12-XXXXSCXXX

| INSERT CODE |                 |
|-------------|-----------------|
| 005A        | 5 POSITION, STD |



INSERT ARRANGEMENT 005A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A

**AirBorn**  
Georgetown, Texas 78626


RECEPTACLE, SIZE 12  
JAM NUT, IST  
SOCKETS, CRIMP

DRAWING STATE: *Released* ☒ **RELEASED**  
This drawing is not authorized for production unless it is released  
DWG# TMR-JSXX12-XXXXSCXXX REV. - SHEET 2 / 3

SIZE  
C

TMR-JSXX12-XXXXSCXXX

| INSERT CODE |                  |
|-------------|------------------|
| 018A        | 18 POSITION, STD |



INSERT ARRANGEMENT 018A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A