

TMR-JTXX12-XXXXSCXXX

KEYING OPTIONS	
A	LIGHT BROWN
B	RED
C	BLUE
D	GREEN



CONTACT FINISH	
0	GOLD

TERMINATION SIZE	
0	STANDARD



INSERT CODE	
005A	5 POSITION, STD
018A	18 POSITION, STD

HOUSING FINISH	
N	TIN NICKEL


HOUSING MATERIAL	
A	ALUMINUM




ISOMETRIC VIEW  
FOR REFERENCE ONLY  
TMR-JTAN12-018ASC00A SHOWN




KEYING OPTIONS (VIEW LOOKING AT RECEPTACLE FACE)




KEY A  
COLOR: LIGHT BROWN



KEY B  
COLOR: RED




KEY C  
COLOR: BLUE



KEY D  
COLOR: GREEN

NOTES:

- SEE ESG6092 FOR MATERIAL AND PERFORMANCE SPECIFICATIONS
- SEE ESG6093 FOR ASSEMBLY INSTRUCTIONS
- SIZE 16 SOCKET CONTACTS PER M39029/57-358
- SIZE 22D SOCKET CONTACTS PER M39029/57-354
- SIZE 20MD SOCKET CONTACTS PER AIRBORN TMC-S20MD
- SPANNER WRENCH PART NUMBER: TMT-N0012
- TORQUE NUT TO 88.5±8 IN-LB [10±1 Nm]



MATERIAL: SEE NOTES		UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE: Decimals: .XX ± 0.01 Concentricity: Decimals: .XXX ± 0.008 Angles: ± 1° Decimals: .XXXX ± 0.0040 Radius: ± Parts are to be symmetrical about centerline within ± .005 Surfaces to be flat, perpendicular parallel within .004 T.I.R. Dimensions are in inches/DO NOT SCALE PRINT Surface finish to be $\sqrt{\text{ }}$ or better		<b>AirBorn</b> Georgetown, Texas 78626		Cage Code 10400	
HEAT TREAT: SEE NOTES		APPLICATION: TRIMATE SERIES		DRAWING STATE: Released		<input checked="" type="checkbox"/> RELEASED This drawing is not authorized for production unless it is released	
Per Spec.: Certification required: NO		- INITIAL RELEASE		DR. CC 060923		TITL E	
Per Spec.: Certification required: NO		REV DESCRIPTION		DR. BY DATE		RCS 060923	
MAKE FROM: N/A		▶ = CRITICAL CHARACTERISTIC		THIRD ANGLE PROJECTION		REL. CC 060923	
NEXT ASSY: N/A		● = MAJOR CHARACTERISTIC		APPD. RCS 060923		DWG# TMR-JTXX12-XXXXSCXXX	
						REV. SHEET 1/3	

D




C

B

A

TMR-JTXX12-XXXXSCXXX

INSERT CODE	
005A	5 POSITION, STD



INSERT ARRANGEMENT 005A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A

**AirBorn**  
Georgetown, Texas 78626

RECEPTACLE, SIZE 12  
JAM NUT, THREADED EXIT  
SOCKETS, CRIMP


DRAWING STATE: *Released* ☒ **RELEASED**  
This drawing is not authorized for production unless it is released  
DWG# TMR-JTXX12-XXXXSCXXX REV. - SHEET 2 / 3

SIZE  
C



TMR-JTXX12-XXXXSCXXX

INSERT CODE	
018A	18 POSITION, STD



INSERT ARRANGEMENT 018A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A

**AirBorn**  
Georgetown, Texas 78626

RECEPTACLE, SIZE 12  
JAM NUT, THREADED EXIT  
SOCKETS, CRIMP

DRAWING STATE: *Released* ☒ **RELEASED**  
This drawing is not authorized for production unless it is released  
DWG# TMR-JTXX12-XXXXSCXXX REV. SHEET  
- 3 / 3

SIZE  
C