

TMR-LSXX09-XXXXPCXXX

|                |             |
|----------------|-------------|
| KEYING OPTIONS |             |
| A              | LIGHT BROWN |
| B              | RED         |
| C              | BLUE        |
| D              | GREEN       |


|                |      |
|----------------|------|
| CONTACT FINISH |      |
| 0              | GOLD |

|                  |          |
|------------------|----------|
| TERMINATION SIZE |          |
| 0                | STANDARD |



|             |                  |
|-------------|------------------|
| INSERT CODE |                  |
| 008A        | 8 POSITION, STD  |
| 010A        | 10 POSITION, STD |

|                |            |
|----------------|------------|
| HOUSING FINISH |            |
| N              | TIN NICKEL |

|                  |          |
|------------------|----------|
| HOUSING MATERIAL |          |
| A                | ALUMINUM |



ISOMETRIC VIEW  
FOR REFERENCE ONLY  
TMR-LSAN09-010APC00A SHOWN



KEYING OPTIONS (VIEW LOOKING AT RECEPTACLE FACE)

KEY A  
COLOR: LIGHT BROWN

KEY B  
COLOR: RED

KEY C  
COLOR: BLUE

KEY D  
COLOR: GREEN


- NOTES:
- 1. SEE ESG6092 FOR MATERIAL AND PERFORMANCE SPECIFICATIONS
  - 2. SEE ESG6093 FOR ASSEMBLY INSTRUCTIONS
  - 3. SIZE 22D PIN CONTACTS PER M39029/58-360



|  |  |   |  |   |  |  |  |
|--|--|---|--|---|--|--|--|
| MATERIAL: SEE NOTES                      |  | UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE:<br>Decimals: .XX ± 0.01      Concentricity:<br>Decimals: .XXX ± 0.008      Angles: ± 1°<br>Decimals: .XXXX ± 0.0040      Radius: ±<br>Parts are to be symmetrical about centerline within ± .005<br>Surfaces to be flat, perpendicular parallel within .004 T.I.R.<br>Dimensions are in inches/DO NOT SCALE PRINT<br>Surface finish to be $\sqrt{\text{ }}$ or better |  | <b>AirBorn</b><br>Georgetown, Texas 78626 |  | Cage Code<br>10400                           |  |
| HEAT TREAT: SEE NOTES                    |  | APPLICATION: TRIMATE SERIES   |  | DRAWING STATE: Released                   |  | <input checked="" type="checkbox"/> RELEASED |  |
| Per Spec.:<br>Certification required: NO |  | - INITIAL RELEASE   |  | DR. CC 060923                             |  | T I T L E                                    |  |
| FINISH: SEE NOTES                        |  | REV DESCRIPTION   |  | DR. BY DATE                               |  | RCS 060923                                   |  |
| Per Spec.:<br>Certification required: NO |  | ECO NO. APPD. BY  |  | REL. CC 060923                            |  | RECEPTACLE, SIZE 9                           |  |
| MAKE FROM: N/A                           |  | THIRD ANGLE PROJECTION  |  | APPD. RCS 060923                          |  | IN-LINE, 1ST PINS, CRIMP                     |  |
| NEXT ASSY: N/A                           |  | DWG# TMR-LSXX09-XXXXPCXXX   |  | REV. 1/3                                  |  | SHEET 1/3                                    |  |

TMR-LSXX09-XXXXPCXXX


| INSERT CODE |                 |
|-------------|-----------------|
| 008A        | 8 POSITION, STD |



INSERT ARRANGEMENT 008A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A

TMR-LSXX09-XXXXPCXXX

| INSERT CODE |                  |
|-------------|------------------|
| 010A        | 10 POSITION, STD |



INSERT ARRANGEMENT 010A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A