




TMR-LSXX09-XXXXSCXXX

KEYING OPTIONS	
A	LIGHT BROWN
B	RED
C	BLUE
D	GREEN
CONTACT FINISH	
0	GOLD
TERMINATION SIZE	
0	STANDARD
INSERT CODE	
008A	8 POSITION, STD
010A	10 POSITION, STD
HOUSING FINISH	
N	TIN NICKEL
HOUSING MATERIAL	
A	ALUMINUM



ISOMETRIC VIEW  
FOR REFERENCE ONLY  
TMR-LSAN09-010ASC00A SHOWN



KEYING OPTIONS (VIEW LOOKING AT RECEPTACLE FACE)

KEY A COLOR: LIGHT BROWN	KEY B COLOR: RED
KEY C COLOR: BLUE	KEY D COLOR: GREEN




- NOTES:
- 1. SEE ESG6092 FOR MATERIAL AND PERFORMANCE SPECIFICATIONS
  - 2. SEE ESG6093 FOR ASSEMBLY INSTRUCTIONS
- ⚠ SIZE 22D SOCKET CONTACTS PER M39029/57-354



MATERIAL: SEE NOTES		UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE: Decimals: .XX ± 0.01      Concentricity: Decimals: .XXX ± 0.008      Angles: ± 1° Decimals: .XXXX ± 0.0040      Radius: ± Parts are to be symmetrical about centerline within ± .005 Surfaces to be flat, perpendicular parallel within .004 T.I.R. Dimensions are in inches/DO NOT SCALE PRINT Surface finish to be $\sqrt{\text{ }}$ or better		<b>AirBorn</b> Georgetown, Texas 78626		Cage Code 10400	
HEAT TREAT: SEE NOTES		APPLICATION: TRIMATE SERIES		DRAWING STATE: Released		<input checked="" type="checkbox"/> RELEASED	
Per Spec.: R/M P/N ref: N/A Certification required: NO		- INITIAL RELEASE		DR. CC 060923		T I T L E	
Per Spec.: Certification required: NO		REV DESCRIPTION		CK. RCS 060923		RECEPTACLE, SIZE 9	
Per Spec.: Certification required: NO		MAKE FROM: N/A		REL. CC 060923		IN-LINE, 1ST	
NEXT ASSY: N/A		▶ = CRITICAL CHARACTERISTIC		THIRD ANGLE PROJECTION		RCS 060923	
						DWG# TMR-LSXX09-XXXXSCXXX	
						REV. SHEET	
						1/3	

TMR-LSXX09-XXXXSCXXX


INSERT CODE	
008A	8 POSITION, STD



INSERT ARRANGEMENT 008A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A

TMR-LSXX09-XXXXSCXXX

INSERT CODE	
010A	10 POSITION, STD



INSERT ARRANGEMENT 010A  
FIGURES SHOWN ASSEMBLED WITH KEY OPTION A