

Switches Power Switches

Slim Type Single Pole Rocker Power Switch SDDJF1A Series

Part number

SDDJF1A100

! Not Recommended for New Designs ?



Reference Drawings



Inquiry



Print

Type	Rocker		
Circuit arrangement	SPST		
Travel	4.6mm		
Operating force	3±2N		
Mounting method	Snap-in		
Dimensions (W×D×H)	30.5×6.0×17.0mm		
SEMKO	16(6)/250~ 8A/128A 250V~		
Operating temperature range	-10°C to +55°C		
Rating	8A/128A 250V~ 16(6)/250~		
Electrical performance	Contact resistance	100mΩ max.	
	Insulation resistance	500MΩ min. 500V DC	
	Voltage proof	2000V AC for 1 minute	
Mechanical performance	Terminal strength	50N for 1minute	
	Actuator strength	Operating direction	25N
		Perpendicular direction	25N
Durability	Operating life	10,000 cycles 10A 250V AC	
Environmental performance	Cold	-20°C 96h	
	Dry heat	85°C 96h	
	Damp heat	40°C, 90 to 95%RH 96h	
Minimum order unit(pcs.)	Japan	150	
	Export	750	