







NOTES:

1. MATERIALS AND FINISHES:
BODY - BRASS,GOLD PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE, NATURAL
CAP - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC 0-6 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: - 65 °C to + 165 °C
4. PACKAGING:
A. PACKAGE IN TAPE,TAPE MATERIAL:BLACK POLYSTYRENE
B. PACKING TAPE LENGTH PER 13" REEL 8.7 METERS.
C. PACKAGE QUANTITY: 650 PCS/ REEL.
D. REEL TO BE MARKED: AMPHENOL RF
252117-75TR
DATE CODE

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	06-Nov-15	----	ZZ
B	SYNC, ADDED PN	31-Oct-17	05643	SH
C	SYSTEM RELEASE	16-Nov-17	05827	BMG



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ±1°	MATERIAL -	DRAWN M.ZHANG	DATE 16-Nov-17	TITLE MCX P.C. BOARD RECEPT. JACK (SURFACE MOUNT - 75 OHMS), TAPE & REEL		Amphenol RF www.amphenolrf.com	
		ENGINEER F.WANG	DATE 09-Nov-15				
		REFERENCE ADDED A CAP,PACKAGE WITH TAPE & REEL BASIC ON MCX6251B4-3GT30G-75	DATE 16-Nov-17	SCALE: 12.0:1.0 SHEET 2 OF 2		DRAWING NO.MCX6251B4-010-3GT30G-75	
		FINISH	CAD FILE	DWG SIZE B		REV C	ITEM NO. 086251ADUAIGE7F PART NO. 252117-75TR