

1		2		3		4		5		6		7																																																																																									
SIGN		DATE		DESCRIPTION						APPROVER																																																																																											
				THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																																																																	
Material: ● Item ① Terminal(housing): Thermoplastic (UL94V-0) ● Item ② Contact pin: Brass,Bright Tin plated over Nickel plated Electrical: cULus ● Voltage rating: 300V ● Current rating: 10A ● Withstanding Voltage: 1.6KV ● Operating temperature: -40°C to +115°C ● Soldering temperature: 260°C±5°C/5 Sec ● Safety Approval: ● Critical dimension:																																																																																																					
P.C.B. LAYOUT																																																																																																					
<table border="1"><tr><td colspan="2">TITLE</td><td colspan="12">OP-3.5mm series (L=12.5 Ø1.0)</td></tr><tr><td colspan="2">PART NO.</td><td colspan="6">OP0422000001G</td><td colspan="2">DWG NO.</td><td colspan="6">80P0117</td></tr><tr><td colspan="2">APPROVED</td><td colspan="2">CHECKED</td><td colspan="2">DESIGNED</td><td colspan="2">DRAWN</td><td colspan="2">CUST NO.</td><td colspan="4"></td><td colspan="2">Tolerance</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">Evan 11/19-15</td><td colspan="2">Evan 11/03-15</td><td colspan="2"></td><td colspan="2">UNIT: mm</td><td colspan="2">X. ±0.50</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2">SHEET: 01/01</td><td colspan="2">SCALE: NONE</td><td colspan="2">X.X ±0.30</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2">REV.: B</td><td colspan="2">X° ±1°</td></tr></table>														TITLE		OP-3.5mm series (L=12.5 Ø1.0)												PART NO.		OP0422000001G						DWG NO.		80P0117						APPROVED		CHECKED		DESIGNED		DRAWN		CUST NO.						Tolerance						Evan 11/19-15		Evan 11/03-15				UNIT: mm		X. ±0.50										SHEET: 01/01		SCALE: NONE		X.X ±0.30												REV.: B		X° ±1°	
TITLE		OP-3.5mm series (L=12.5 Ø1.0)																																																																																																			
PART NO.		OP0422000001G						DWG NO.		80P0117																																																																																											
APPROVED		CHECKED		DESIGNED		DRAWN		CUST NO.						Tolerance																																																																																							
				Evan 11/19-15		Evan 11/03-15				UNIT: mm		X. ±0.50																																																																																									
								SHEET: 01/01		SCALE: NONE		X.X ±0.30																																																																																									
										REV.: B		X° ±1°																																																																																									
1		2		3		4		5		6		7																																																																																									