








NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- HIGH POWER CONTACTS 30A: COPPER ALLOY
PLATING, MATING AREA: GOLD FLASH over NICKEL
PLATING, TERMINATION SIDE: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 10-12

5. CONNECTOR IS PART MARKED: 3007W2SAM63A10X CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance				 dim. in mm		scale: 2:1 (5:1)								
																material: SEE NOTES								
															date	name			title: D-SUB COMBINATION FEMALE 7W2S SOLDER CUP					
															drawn	06.01.2015 Heinrich								
															appd.	06.01.2015 Lehmenkühler								
															norm									
															d-old				dwg no:				DIN-A3	
											a	Original												
											rev.	description	date	name										13K1A4859
										part no:				3007W2SAM63A10X										
														sh: 1										