


RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2024.05.17	The first release	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



Technical Specification:

- Current: 35A.
- Torque: 13 lbf.in.
- Mark"▲" is the Critical dimension.

⑥	Spacer	Steel , Matte Tin Plated	1PCS
⑤	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES I N ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR.PROPERTY OF ANYTEK TECHNOLOGY CO., LTD				
TITLE		AMT44007DB Conductive Bracket						
PART NO.		AMT0440007DB0000G		DWG NO.	8AMT0011			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Guoxue 2024.05.17	Guoxue 2024.05.17		UNIT: mm SCALE: NONE		>30 ±0.60	±0.60
				SHEET: 01/01	REV.: B		6-30 ±0.40	±0.40
							0-6 ±0.30	±0.30
							ANGLES	±1°