


RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2024.05.14	The first release	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Technical Specification:

- Current: 30A.
- Torque: 13 lbf.in.
- Mark"▲" is the Critical dimension.



⑥	Spacer	Steel , Matte Tin Plated	1PCS
①	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q`ty

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUTWRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD					
TITLE		AMT44049DB Conductive Bracket							
PART NO.		AMT0440049DB0000G		DWG NO.		8AMT0017			
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance	
			Guoxue 2024.05.14	Guoxue 2024.05.14				UNIT: mm	>30 ±0.60
						SCALE: NONE		6-30 ±0.40	
						SHEET: 01/01		0-6 ±0.30	
						REV.: B		ANGLES ±1°	