





RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2024.05.15	The first release	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



Technical Specification:

1. Current: 70A.
2. Torque: 15 lbf.in.
3. Mark "▲" is the Critical dimension.

②	Spacer	Steel, Matte Tin Plated	1PCS
①	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q'ty

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE AMT45001DB Conductive Bracket

PART NO. AMT045001DB0000G DWG NO. 8AMT0023

APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Guoxue 2024.05.15	Guoxue 2024.05.15		>30 ±0.60 6-30 ±0.40 0-6 ±0.30 ANGLES ±1°
					UNIT: mm SCALE: NONE SHEET: 01/01 REV.: B