



used for: D-SUB COMBINATION

RoHS compliant

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance	dim. in mm	name
2005	date	29.08.
drawn	Lehmenküller	30.08.
appd.	Mickenbacher	norm
		d-old

scale:	10:1
material:	
title:	COAXIAL CONTACT SOCKET 50 Ohm Solder termination 90° (78) with 3 pins for D-SUB COMBINATION
dwg no:	AutoCAD 2004
part no:	13K21A TA
	DIN-A
	3
	sh: 1/1