




Amphenol Connex

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex								
					DRAWN	M.ZHANG	05/23/12										
					CHECKED				PART DESCRIPTION FERRULE (FOR RG-174/U,188A/U,316/U CABLE)								
					ISSUED												
					SHEET		1 OF 1										
					PART NO. FERRULE-174NEX												
					CAD FILE		DWG. NO.		FERRULE-174NEX .DWG		REV.	NC	SIZE	A	SCALE	NA	
					C:/CONNEX/FERRULE-174NEX .DWG												

1	FERRULE	BRASS	NEXCOTE	1
	DESCRIPTION	MATERIAL	FINISH	QTY