






- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. RECOMMENDED MATING BLADE THICKNESS 0.6 ± 0.03 MM OR 0.64 ± 0.03 MM
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 1.2 MM
AND NO LESS THAN 0.61 MM.

3. MAXIMUM CURRENT CAPACITY IS 10 AMPS WITH 0.8 MM² COPPER CABLE.

4. CRIMP DIMENSION FROM THE BACK OF THE CORE WING (INCLUDES THE

- FLARE OUT FROM THE CORE WING) TO THE END OF THE INSULATION WING

- 2.05 MM MAX WIDTH, 2.1 MM MAX HEIGHT FOR CABLE SIZE UP TO 1.9 MM O.D.
2.35 MM MAX WIDTH, 2.40 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 1.86 TO 2.25 MM O.D.
2.67 MM MAX WIDTH, 2.67 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 2.25 TO 2.40 MM O.D.

5. * DENOTES DIMENSIONS MADE AT CUT-OFF & CRIMP DIE.

6. PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	21
	LAST NO. USED	19

• APTIV • CONNECTION SYSTEMS WARREN, OH COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
						DATE			
DR									
APW01	LUIS VILLARREAL				28FE19				
APW02	ROBERT B SNADER				01MR19				
APW03	ROBERT B SNADER				01MR19				
APW04									
APW05	SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 104949001								
MATERIAL SEE CHART									
DRAWING NAME									
TAXI TERM F OCS 1:2									
DRAWING NUMBER									
13543112									
SIZE	SCALE	FRAME	1	SHEET	NO	REV	NO	REV	N/P
A0	10:1	1	OF	10	OF	R	06		