



HIRSCHMANN

A BELDEN BRAND

Product information STAKEI 2 grau/grey

Industrial Connecting Solutions:Rectangular Connectors:Power Connectors (ST series):Panel-mounted socket:STAKEI 2 grau/grey


<https://e-catalog.hirschmann.com:443/link/57078-24228-256261-24351-24353-35739/en/conf/uistate>

Name		STAKEI 2 grau/grey
		
		Panel-mounted socket, added gasket
Delivery informations		
Availability		available
Product description		
Description		Panel-mounted socket, added gasket
Type		STAKEI 2 grau/grey
Order No.		930 647-106
Type of contact		female
Number of contacts		2 + PE
Conductor size		max. 1.5 mm ²
Housing Color		grey
Contact bearer color		black
Technical data		
Pin dimensions		2 mm
Rated voltage		AC/DC 250 V
Rated current		DC 10 A / AC 16 A
Contact resistance		<= 5 mOhm
Type of termination		screws
Mounting		Schrauben
Material		
Contact material		Cu Zn
Contact surface material		Sn
Contact bearer material		PA
Housing material		PA
Environmental conditions		
Protection class (IEC 60529)		IP 54
Pollution severity		3
Temperature range		-30 °C to +90 °C
Inflammability class		
Housing		UL 94 HB
Contact bearer		UL 94 V-0
Approvals		
UL		UL
VDE		VDE
SEV		SEV
Packing unit		
Packaging unit		100 pieces
Scope of delivery and accessories		
Accessories to order separately		safety brackets STASI 2, order no. 732 044-000

<https://e-catalog.hirschmann.com:443/link/57078-24228-256261-24351-24353-35739/en/conf/ui/estate>

Picture

Drawing



E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.