Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



A0645271 Faceplates and Panels - MDVO Side Entry Box 2 Port







For more Information please call

1-800-Belden1



General Description: MDVO Side Entry Box 2 Port Usage (Overall) Suitable Applications: Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1200. Related Parts: - Compatible with 10GX, CAT6+ and CAT5E MDVO-style Modular Jacks and MDVO Multimedia Modules Physical Characteristics (Connectivity) Capacity 2 ports Max. Capacity: Access Front Connection: Flush **Dimensions** Dimensions: Height (in.) Width (in.) Depth (in.) 2.750 2.000 **Materials** Materials: **Description Material** Side Box Plastic - UL94V-0 Color Color: Gray Weight Weight: 0.220 lbs **Included Parts Included Parts:** adhesive foam pad, installation sheet, #6 screw, **Packaging** Packaging: Individually packaged in a plastic bag. **Mechanical Characteristics (Connectivity)** 20 lbs. Connector/Hardware Retention: Storage Temperature Range: -40°C To +70°C Installation Temperature Range: -10°C To +60°C Operating Temperature Range: -10°C To +60°C Applicable Specifications and Agency Compliance (Overall) **Applicable Standards & Environmental Programs** EU Directive 2002/95/EC (RoHS): Yes EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006 MII Order #39 (China RoHS): Safety Listing: ACA, Bi-national Standard Listed Suitability Suitability - Indoor: Yes **Transmission Characteristics (Connectivity)** Notes (Overall)

Notes: For proper installation refer to Installation Guide P0820423 included with the product or visit our web site at http://www.belden.com

Page 1 of 2 08-16-2017

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



A0645271 Faceplates and Panels - MDVO Side Entry Box 2 Port

Product Family

Part Numbers:

Item Number	Color
A0645271	Gray
A0645272	Almond
A0645273	White
A0645274	Black

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
A0645271	1 EA	0.222 LB			MDVO SIDE ENTRY BOX,

Revision Number: 0 Revision Date: 06-02-2009

© 2017 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/5FC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Page 2 of 2