









Notes:

- Material and Finish:
 - Receptacle Housing: Polyester (Black), UL94 V-0;
 - ② or ABS, Nickel Plated, UL94 V-0,
 - Duplex LC Adaptor Assembly:
 - Housing: Mod. PPO, UL94 V-0,
 - Color: **SM Blue/MM Beige/APC SM Green**
 - Alignment Sleeves: SM Ceramic/MM Phosphor Bronze
 - Dust Cap: PP, Color: Neutral transparent
 - Operating Temperature: -40°C to +85°C
- Connector can be mounted to a maximum panel thickness of 3.2mm.
- IP67 rated when covered or fully mated with the appropriate mating connector

Directive 2002/95/EC RoHS Compliant

Description	Plastic Version	Metallized Version
Single Mode (SM)	17-300790	17-300910
Multi Mode (MM)	17-300800	17-300920
APC Single Mode (APC SM)	17-300810	17-300930

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION IS RESERVED.	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Scale:	Dim. in mm
	Name	Title	Approval Date			Material: See Notes	
						Title: IP67 Industrial Duplex LC Receptacle Assembly Kit	
						Plastic Version with bayonet on both sides	
						Drawing No.: 17K1A332	
Rev.			Changes	Date	Name	Part No.: SEE PART NUMBER TABLE	
c			1 x c	Sep/25/2013	Vincent Ke	DIN A3	
b			3 x b	Jan/18/2013	Vincent Ke	Sheet 1/1	
a			original				

CONEC