



THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.

REV.	BY	DATE	APPRVL.	P/N
B	DMS	3/23/98	BT	DC27F ADDED SHAFT CHART

SPECIFICATIONS

ACCURACY _____ $\pm 0.35\%$ OF VOLTAGE RATIO
REPEATABILITY _____ $\pm 0.02\%$ OR RESOLUTION OF POT
OPERATING TEMPERATURE RANGE _____ -30°C TO 85°C
TURNS _____ 10 (000 TO 999 COUNTS)
LOCK _____ OVER THE CENTER (DC27F"L")
HOUSING MATERIAL _____ HIGH TEMP. BLACK PLASTIC

PANEL LAYOUT



THREAD MAJOR DIA.= 1.10"
REQUIRED MOUNTING HOLE
IN PANEL = 1 1/8" DIA.

NOTES

- COMPATIBLE ETI SYSTEMS POTENTIOMETERS 3 TO 30 TURNS.
MW20B MW46B MH20B
MW22B MR46B MH46B
- POT/DIAL COMBINATIONS AVAILABLE
SEE ETI SPECIFICATION DC22.
- OTHER SHAFT SIZE BUSHINGS AVAILABLE
- NUMBERS INCREASE WITH CLOCKWISE ROTATION

TOLERANCES

XX = $\pm .010"$ FRACT. = $\pm 1/64"$
XXX = $\pm .005"$ ANGLES = $\pm 1/2^{\circ}$

ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

SCALE	DATE: 3/18/98
N/A	BY DMS
CODE	APPRV'D BT
IDENT:	19477



TITLE
TURNS COUNTING DIAL

PART NO.
DC27F